

## Standard Pump Head



**Model No.: SN25**  
**Flow Rate :**  
**0.25-1500mL/min**

### Product Features

- Standard pump head with compact structure, exquisite appearance.
- Fixed occlusion and stable running.
- Can stack several pump heads, and support various equipment.


### Typical Application

Use in the ice cream machine and coffee making machine;  
 Support OCD on-line monitor.

### Technical Specifications

Model No.	Housing Material	Rollers Material	Tubing		Speed Range(rpm)	Flow Rate(mL/min)	Weight(kg)
			Tubing Size	ID×Wall thickness			
SN15-14	PC	304 stainless steel	14#	1.6×1.6(mm)	0.1-600	0.024~144	0.20
SN15-16			16#	3.1×1.6(mm)		0.088~528	
SN25			24#	6.4×2.4(mm)		0.25~1500	

## Tubing Installation



1. Disassemble the pump head, and press the tubing on the rollers.



2. Make the tubing go around the rollers one cycle, and merge it on the exit.



3. Tighten the tubing aptly, and load the other half pump head body.

## Dimension Drawing (Unit:mm)

